



ZENTRIERHÜLSE
LOCATING SLEEVE

⌚ 1.7131 / ~60 HRC

l1	l2	d1	d2	d3	L	€/1
8	2	11	M8	14	20	•
					30	•
					40	•
					50	•
					60	•
					70	•
					80	•
					100	•
13	2	16	M12	20	30	•
					40	•
					50	•
					60	•
					70	•
					80	•
					90	•
					100	•
					110	•
					120	•
					140	•
					160	•
13	2,5	21	M12	26	30	•
					40	•
					50	•
					60	•
					70	•
					80	•
					90	•
					100	•
					110	•
					120	•
					130	•
					140	•
					160	•
					180	•
13	2,5	25	M12	30	40	•
					50	•
					60	•
					70	•
					80	•
					90	•
					100	•
					110	•
					120	•
					130	•
					140	•

l1	l2	d1	d2	d3	L	€/1
13	2,5	25	M12	30	160	•
					180	•
					200	•
					220	•
					240	•
13	4,5	33	M12	42	40	•
					60	•
					80	•
					100	•
					120	•
					140	•
					160	•
					180	•
					200	•
					220	•
					240	•
					260	•
					280	•
					300	•
13	4,5	43	M12	54	60	•
					80	•
					100	•
					120	•
					140	•
					160	•
					180	•
					200	•
					220	•
					240	•
					280	•
					320	•
18	6	54	M12	66	80	•
					100	•
					120	•
					140	•
					160	•
					180	•
					200	•
					240	•
					280	•
					320	•

✉ 50020/d3xL